



## Tender Notice

DSK HQ: House-741, Road-9, BAHS, Adabor, Dhaka-1207, Bangladesh

Telephone: +8802-9128520, 8120965, 58151176;

Fax: +8802-58153413

### A) Specification of Toyota HiAce DX GL Ambulance

1.	<b>Brand Name</b>	<b>Toyota</b>
	Model	HiAce DX GL
	Year of Manuf.	2014
	Transmission	Automatic
	Engine No.	1TR
	Chassis No.	TRH200-0198730
	Engine capacity	2000 CC
	Body Type	MPV
	Fuel type	Octane
	Kilometers run	± 20,0000 Km
	Color	White
	Air cooler	Central Duel AC
	Mileage	Digital Meter
	Air bag	Duel Air Bag
	Accessories	NTB, <b>Back camera</b> , 5D, R/M, <b>Oxygen Cylinder</b> with Bracket, <b>Light Bar with Siren &amp; Mount-Amp.</b> RH/LH side Strobe, <b>Power door</b> , <b>Audio steering</b> , Switch steering, Winker mirror, rain shade-4, CD/DVD <b>15" Alloy Rim &amp; Tier</b> , standard tools, etc..
2.	<b>Registration fee</b>	Included advance Income Tax, Fitness Certificate, Tax Token, etc.
<b>Total Price including VAT+AIT</b>		

### B) Computed Radiography (FCR PRIMA T2)

This compact table-top reader unit has outstandingly high-speed processing to challenge the common misconception of CR.

#### High-speed processing

FCR PRIMA T2 is a table-top reader unit which boasts a world-class high processing speed of 73 IPs/hour. In the high speed mode (5 pixels/mm), throughput is enhanced almost 70% compared with FCR PRIMA T (only for IPs of 14" × 17" and 14" × 14"). As with all Fujifilm equipment FCR PRIMA T2 is easy to operate. It will help reduce patient waiting time and greatly increase the efficiency of examination workflow.

### Space-saving design

FCR PRIMA T2, with its light and compact table top design, can be placed on a desk, shelf or anywhere space is limited. As this is a fully digital reader, neither a darkroom nor automatic processor is required. FCR PRIMA T2 can always be installed in the space formally used by a chemistry based processor.

### Stable high-quality images

Although this is a compact machine its excellent image quality is the same as that produced by the rest of the FCR range. Image Intelligence™, Fujifilm's proprietary image processing technology, enhances image contrast and sharpness, without any deterioration of details. FCR PRIMA T2 supports accurate diagnosis by offering stable and optimized image quality.

### **MFP (Multi-Frequency Processing) \***

Enhances FCR images. All diagnostic scopes will be enhanced except for noise.

- Optional Software
- FNC (Flexible Noise Control)  
Provides a non-grainy image by mainly isolating and suppressing the noise for the signal

### **GPR (Grid Pattern Removal)**

Removes the stationary grid patterns thus preventing Moiré from being generated resulting in easier diagnosis.

### At a Glance of Fujifilm Brand Computed Radiography (CR)

1. High Quality Fuji FCR Model (prima T2)
2. FCR Console (Computer) with High Resolution Monitor
3. Related Software
4. Dry Digital Printer (Drypix LITE)
5. With standard cassette & imaging plate and UPS
6. Manufacturer FUJIFILM Corporation, Japan

### **Terms and Conditions:**

1.	<b>Time limit</b>	Goods and accessories should be provided within 15 business days from receipt of the Work Order, otherwise the bill will be deducted at 1% of the net due bill for every 5 days.
2.	<b>Deduction of IT &amp; VAT</b>	Income Tax and VAT must be included in your quoted price. According to the government policy, applicable IT and VAT or any other charges as per govt. rule will be deducted at source from your bill. Within 15 days of receipt the bill, Income Tax and VAT papers will be collected by the Vendor at their own risk.
3.	<b>Mode of payment</b>	Overwrite, torn, rub is not acceptable on Tenders & Bill. DSK will not provide any kind of advance for purchasing the Vehicle. Payment will be made after delivery the goods/vehicle and/ or complete installation of goods and accessories. After received the goods within 15 days, the bill will be paid by A/C Payee Cheque on your company name.

4.	<b>Communication</b>	If you have any confusion or queries please do call with Md. Nurul Haque Mallik, Cell: 01926673233 asap.
5.	<b>Cancellation</b>	DSK authority reserves the right to accept or cancel any of the quotations in full or part without assigning any reason.
6.	<b>Others</b>	Within 3 days of opening the tender, the Work Order will be issued by DSK, otherwise the said tender will be canceled.
7.	<b>Return of materials</b>	Substandard Ambulance & accessories will not be accepted by DSK and no payment will be made for it.

### **C) Complete Steel Structure for Lift**

Complete Structure with supplying all materials, fabrication & erection of steel structure with structure base, structure wall and roofing.

### **D) Original China Branded 8 passenger Lift**

Collective control, VVVF Inverter driving system, Microcontrol, Digitally Pulsed Type, Digital indicator of floor, Car side wall & Car rear wall & Operating panel board, ground floor Hairline stainless steel finish. Included all safety. Without machine room.

#### **Quick Details**

Type	:	Elevators
Place of Origin	:	China
Usage	:	Business Elevators
Drive Type	:	AC
Elevator Type	:	Passenger Elevators
Product name	:	Passenger Lift
Certification	:	ISO9001/CE
Keywords	:	VVVF Passenger Elevator
Control	:	Monarch Nice 3000
Material	:	Stainless Steel
Rated Speed	:	1.0~4.0m/s (Elevator)
Capacity	:	1000 Kg??
Load capacity	:	8 Persons??
Application	:	DSK Hospital Building
Item Name	:	High Standard Passenger Elevator

#### **Packaging & Delivery**

Packaging Details	:	The corresponding and qualified oversea wooden cases
-------------------	---	--